

# MESOTRON

Quartz table stopclock

zu beziehen bei

sold by

[www.conatex.com](http://www.conatex.com)



## Preparation

Remove the battery-cover located under the base. When changing the battery type AA of 1,5 V, respect polarity. Replace battery cover. Reset the stopwatch by pressing the black button.

## Functions

1. start: press the red button  
stop: press the red button  
reset: press the black button
2. addition: press the red button consecutively as often as required
3. tempo: start-reset with automatic starting of the second hand. Press red button and then the black one as often as requested.

## Technical data

movement:	quartz controlled 32,768 Khz
accuracy:	+/- 14 sec./month
dial:	first hand 60 min. second hand 60 sec. - 100/100 min. diameter 110 mm ø
time units:	1 sec. and 1/100 min.
case:	ABS, 175 x 130 x 40/95 mm
weight:	370 g approx.
battery:	Mignoncell 1,5 V (AA)
duration:	1 1/2 years
battery life indicator:	in case of critical battery capacity, the hand is not running smoothly (0,75-1,25-0,75-1,25...) sec. Then there is only power left for about 1 week
temperature in use:	-10° C to + 60° C

This product is German made.